# Specifications SMART Response<sup>™</sup> LE interactive response system

# **Receiver and clicker**

#### Physical specifications

**Receiver size** 

Receiver weight Clicker size


#### Clicker weight Shipping size

32 and 24 Clicker System (SRP-LE-32/SRP-LE-24)

18 and 12 Clicker System (SRP-LE-18/SRP-LE-12) Shipping weight 4 3/4" W × 7/8" H × 2 1/4" D (12 cm × 2.2 cm × 5.7 cm) 5 3/4 oz. (165 g) 2 1/4" W × 5 5/8" H × 1 1/8" D (5.7 cm × 14.2 cm × 2.8 cm) 7 1/4 oz. (200 g) without batteries

22 5/8" W × 7 3/4" H × 13 5/8" D (57.5 cm × 19.8 cm × 34.5 cm)

17 1/2" W × 11" H × 8 3/8" D (44.4 cm × 27.9 cm × 21.1 cm) SRP-LE-32 – 14 lb. (6.4 kg) SRP-LE-24 – 12 lb. (5.4 kg) SRP-LE-18 – 10 lb. (4.5 kg) SRP-LE-12 – 8 lb. (3.7 kg)



All dimensions +/- 1/8" (0.3 cm). All weights +/- 2 lb. (0.9 kg).

### Standard features

SoftwareSMART Response™ 2010 assessment software, including SMART Notebook™<br/>collaborative learning software 10, for Windows® and Mac computers is included on<br/>the DVD. Software upgrades are available at <a href="mailto:smarttech.com/Downloads">smarttech.com/Downloads</a>.TechnologyRF 802.15.4Radio frequency2.40 GHz to 2.50 GHz ISM band

Capacity Supports up to 60 clickers with Model 1.1.3 receiver

Extraordinary made simple<sup>™</sup>



2 | SPECIFICATIONS -

#### Windows operating Pentium® III 750 MHz or later processor systems 512 MB of RAM (1 GB recommended) 800 MB of free hard disk space for minimum installation (2150 MB for full installation with Gallery collections) Windows XP, Windows Vista® or Windows 7 operating system Internet Explorer® Internet browser 6.0 or later Adobe® Flash® Player 10 plug-ins for Internet Explorer and Firefox® browsers (provided with SMART Response) Adobe Reader® 8.0 or later Windows Media® Player 9 (required for SMART Recorder) Microsoft® DirectX® application programming interface 8.1 or later (required for SMART Video Player) Mac operating system 1 GHz PowerPC® G4 or G5 processor or Intel® processor (universal binary) software 1 GB of RAM 800 MB of free hard disk space for minimum installation (2 GB for full installation with Gallery collections) Mac OS X 10.5.8 or 10.6.x operating system software Safari application program 3.0.4 or later Adobe Flash Player 10 plug-in (provided with SMART Response) NOTES ٠ SMART Response assessment software runs on 32-bit Windows and Mac operating systems. You're unable to use SMART Response software on Windows computers with

Intel Itanium® processors.

### SMART Response software computer requirements

3 | SPECIFICATIONS -

### **Receiver features**

Transmission power	6 dBm with a typical range of 100' (30 m)	
Antenna	Integrated antenna	
Host interface	USB 2.0 full-speed (12 Mbps) with a 6' (1.8 m) captive cable	
LED indicators	Red and green LED indicate power, transmit data, receive data and link status.	
Configuration	Plug and play (SMART Response software required)	

## Clicker features

Transmission power	6 dBm with a typical range of 100' (30 m)	
Antenna	Integrated antenna	
LCD display	1 5/8" W $\times$ 1" H (41.6 mm $\times$ 24.6 mm), 60° to 80° viewing angle and a contrast ratio of 5:1	
Key pad	Buttons include: GREEN/CIRCLE, RED/TRIANGLE, BLUE/SQUARE, YELLOW/ STAR, PURPLE/DIAMOND, ? (QUESTION MARK), UP, DOWN, HOME, ENTER, POWER	
Configuration	Plug and play (no additional software required)	
Batteries	2 × AA alkaline	
Regulatory certification	IC (Industry Canada), C-Tick, CE, FCC, SRRC (Pending), NOM (Pending)	
Environmental compliance	EU WEEE, RoHS (Europe), US CPSIA, US Packaging, China EIP	
Warranty	Two-year limited equipment warranty	
	Storage and operating specifications	

#### Storage and operating specifications

Operating temperature	41°F to 95°F (5°C to 35°C)
Operating humidity	5% to 85% relative humidity (non-condensing)
Storage temperature	-40°F to 131°F (-40°C to 55°C)
Storage humidity	5% to 90% relative humidity (non-condensing)

4 | SPECIFICATIONS -


#### SMART order numbers

- **SRP-LE-32** Includes 1 receiver, 32 clickers, carrying case for 40 clickers, Phillips® No. 1 screwdriver, 64 AA batteries, *SMART Response LE Quick Start Guide* and software DVD
- **SRP-LE-24** Includes 1 receiver, 24 clickers, carrying case for 40 clickers, Phillips No. 1 screwdriver, 48 AA batteries, *SMART Response LE Quick Start Guide* and software DVD
- **SRP-LE-18** Includes 1 receiver, 18 clickers, carrying case for 20 clickers, Phillips No. 1 screwdriver, 36 AA batteries, *SMART Response LE Quick Start Guide* and software DVD
- **SRP-LE-12** Includes 1 receiver, 12 clickers, carrying case for 20 clickers, Phillips No. 1 screwdriver, 24 AA batteries, *SMART Response LE Quick Start Guide* and software DVD


#### **Optional accessories**

- SRP-LE-RMT-5 Includes 5 clickers and 10 AA batteries
- SRP-LE-RMT-1 Includes 1 clicker and 2 AA batteries
- SRP-LE-RCV-1 Includes a receiver and software DVD
- SRP-LE-CC Carrying case for 1 receiver and 40 clickers
- SRP-LE-CC-SM Carrying case for 1 receiver and 20 clickers

#### **Physical dimensions**



#### **Viewing angle**



www.smarttech.com/support www.smarttech.com/contactsupport Support +1.403.228.5940 or Toll Free 1.866.518.6791 (U.S./Canada)



© 2007–2010 SMART Technologies ULC. All rights reserved. SMART Response, SMART Notebook, The SMART logo and smarttech are trademarks or registered trademarks of SMART Technologies ULC in the U.S. and/or other countries. Windows, Windows Media, Windows Vista, Internet Explorer and DirectX are either registered trademarks or trademarks of Microsoft Corporation in the U.S. and/or other countries. Mac and Safari are registered trademarks of Apple, Inc. Adobe, Reader and Flash are either registered trademarks or trademarks of Adobe Systems Incorporated in the U.S. and/or other countries. All other third-party product and company names may be trademarks of their respective owners. Patent No. US6320597; US6326954; US6741267; US7151533; US7499033; and CA2252302. Other patents pending. Contents are subject to change without notice. 09/2010.